

NOVATECH

ETP 082X76-Ø20 HL76

EAN 4031582318722

Broj porudžbine 00827955



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	82 mm
Širina omotac	76 mm
dimenzija rupa osovina	20 mm
dužina glavcine	76 mm
Širina tela	76 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6204

PERFORMANSE

Performanse kotrljanja ● ● ● ● ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	840 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,16 kg

NOVATECH

ETP 082X76-Ø20 HL76

EAN 4031582318722

Broj porudžbine 00827955



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

