

MAXTECH

PA0075X25-Ø6X27 + ASBUS

EAN 4031582381238



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	132.28 lb
Load capacity Static	264.55 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.17 lb

WHEEL

Diameter	2.95 in
Tread width	0.98 in
Axle hole diameter	0.24 in
Hub length	1.06 in