

AGILA

2477DYK100R07-Ø24-27

EAN 4031582342215



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric conductive	✓
Load capacity Static	160 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	138 mm

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	43.5 mm
Swivel radius	131 mm
Swivel interference	262 mm

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	24 mm
Expander fitting (Maximum)	27 mm
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2477DYK100R07-Ø24-27

EAN 4031582342215



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

