

# DURATECH

TOP 085X60-Ø20 HL60

EAN 4031582331165

Broj porudžbine 00832610



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	85 mm
Širina omotac	60 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Širina tela	60 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	650 kg
Nosivost na 6 km/h	520 kg
Statički Nosivost	1300 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,513 kg

# DURATECH

TOP 085X60-Ø20 HL60

EAN 4031582331165  
Broj porudžbine 00832610



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

