PRODUCT INFORMATION

DURATECH HEAT

WOG 075x25 HL27 black

EAN 4031582382884



Image may differ from the original product

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Wheel Color	Black
Diameter	75 mm
Tread width	25 mm
Axle Hole Diameter	8 mm
Hub Length	27 mm
Body width	25 mm
Hardness of tread (D)	80 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●○○○
Attrition	●●●●●
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	100 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	134 °C
Overall weight	0.08 kg

© Copyright 2026 TENTE International GmbH


DURATECH HEAT

WOG 075x25 HL27 black

EAN 4031582382884

Order number 00039930

Product Drawings



© Copyright 2026 TENTE International GmbH