

# ANIKA

5925PJI065L51-10 DOM18 9011-7015

EAN 4031582437010



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Anika                          |
| Housing type                | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 3 km/h     | 40 kg                          |
| Load capacity Static        | 80 kg                          |
| Temperature range (Minimum) | -10 °C                         |
| Temperature range (Maximum) | 40 °C                          |
| Overall height              | 67 mm                          |
| Overall width               | 39.5 mm                        |
| Overall weight              | 0.084 kg                       |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Threadguards          | Without threadguard            |
| Diameter              | 65 mm                          |
| Tread width           | 11 mm                          |
| Hardness of tread (A) | 87 Shore A                     |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Swivel radius       | 76 mm              |
| Swivel interference | 152 mm             |
| Dome diameter       | 18 mm              |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 10 mm                      |

## PRODUCT INFORMATION

# ANIKA

5925PJI065L51-10 DOM18 9011-7015


EAN 4031582437010



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---



Interzum  
Award