

# ALPHA

3470UER100P30-13

EAN 4031582304312



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	128 mm
Overall weight	0.857 kg

## WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, black, vulcanized
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	100 mm
Tread width	34 mm
Hardness of tread (A)	64 Shore A

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	40 mm
Swivel radius	90 mm
Swivel interference	180 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

# ALPHA

3470UER100P30-13

EAN 4031582304312



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

3470...100P30-13

