PRODUCT INFORMATION

PURETECH

UVH 080x35 HL46

EAN 4031582323627

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Solid rubber, black
Bearing	Plain bearing
Wheel color	Graphite black (RAL9011)
Threadguards	With threadguard
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.33 in
Hub length	1.81 in
Body width	1.38 in
Hardness of tread (A)	90 Shore A
Hardness of tread (D)	39 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	0.48 lb

© Copyright 2026 TENTE International GmbH


PURETECH

UVH 080x35 HL46

EAN 4031582323627

Order number 00002549

Product Drawings



© Copyright 2026 TENTE International GmbH