

# AGILA

267FPJP3.5X1.25P30-13

EAN 4031582435191



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                  |           |
|------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise   | ● ● ○ ○ ○ |
| Attrition        | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                         |                                              |
|-------------------------|----------------------------------------------|
| Product name            | Agila                                        |
| Housing type            | Castor with butterfly wheel brake            |
| Standard                | Institute of Casters and Wheel Manufacturers |
| Load capacity at 3 km/h | 95 kg                                        |
| Load capacity Static    | 190 kg                                       |
| Overall height          | 112.7 mm                                     |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 88.9 mm                |
| Tread width           | 31.75 mm               |
| Axle hole diameter    | 10 mm                  |
| Hardness of tread (A) | 77 Shore A             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad, reinforced   |
| Swivel bearing      | Two ball races      |
| Offset              | 34 mm               |
| Swivel radius       | 78.5 mm             |
| Swivel interference | 157 mm              |

## FITTING

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Fitting type       | Bolt hole                                                  |
| Bolt hole diameter | 13 mm                                                      |
| Hint               | Castors can be mounted with standard screws of any length. |