

# PURETECH AIR

DQR260x85-Ø25 HL74 4PR

EAN 4031582318111



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                               |
|-----------------------|-------------------------------|
| Tread hardness        | soft                          |
| Body material         | Sheet Steel                   |
| Tread Material Mix    | Pneumatic tyre, block profile |
| Bearing               | Roller bearing                |
| Threadguards          | Without threadguard           |
| Diameter              | 260 mm                        |
| Tread width           | 85 mm                         |
| Axle Hole Diameter    | 25 mm                         |
| Hub Length            | 74 mm                         |
| Hardness of tread (A) | 55 Shore A                    |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ○ ○ ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                         |              |
|-------------------------|--------------|
| Product Name            | Puretech air |
| Type                    | Wheel        |
| Load capacity at 3 km/h | 150 kg       |
| Electric Conductive     | No           |
| Stainless               | No           |
| Load capacity Static    | 300 kg       |
| Overall weight          | 1.35 kg      |

# PURETECH AIR

DQR260x85-Ø25 HL74 4PR

EAN 4031582318111



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

