

NOVATECH

FTP200X75-Ø25 HL75

EAN 4031582428827



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Casting |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 7.87 in |
| Tread width | 2.95 in |
| Axle hole diameter | 0.98 in |
| Hub length | 2.95 in |
| Hardness of tread (A) | 92 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|----------|
| Product name | Novatech |
| Housing type | Wheel |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 17.61 lb |

TECHNICAL DRAWINGS

