

ELASTECH

EEZ250x60-Ø190 DG

EAN 4031582318340



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Tread hardness	soft
Body material	Steel, iron
Tread Material Mix	Elastic tire, black, vulcanized
Bearing	Borehole, unmachined
Diameter	250 mm
Tread width	60 mm
Axle Hole Diameter	190 mm
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	630 kg
Load capacity at 6 km/h	525 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1260 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	1.36 kg




PRODUCT INFORMATION

ELASTECH

EEZ250x60-Ø190 DG

EAN 4034582318340

Order number 00880877



BETTER MOBILITY. BETTER LIFE.