

FOOTMASTER

FOOT MASTER SGDN- 60-F-NYN

EAN 4031582419399



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

CORE ATTRIBUTES

Product Name	Footmaster
Type	Swivel castor
Electric Conductive	No
Stainless	No
Load capacity Static	250 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall Height	82.5 mm
Overall weight	0.5 kg

HOUSING

Offset	36 mm
Swivel radius	63 mm
Swivel interference	126 mm

WHEEL

Body material	Polyamide, super heavy
Tread Material Mix	Polyurethane, injected
Bearing	Roller bearing, damped
Threadguards	Without threadguard
Diameter	50 mm
Tread width	25 mm
Hardness of tread (D)	70 Shore D

FITTING

Plate length	73 mm
Plate width	73 mm
Plate hole length (Maximum)	58 mm
Plate hole width (Maximum)	58 mm
Plate hole diameter	7 mm

FOOTMASTER

FOOT MASTER SGDN- 60-F-NYN

EAN 4031582419399



BETTER MOBILITY. BETTER LIFE.

Product Drawings

