

NOVATECH

ITP 250x50-Ø25 HL60 soft cv

EAN 4031582329629



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK


Tread profile	konveksan
Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglični lezaj
Boja Tocak	Saobraćajna siva A (RAL7042)
stitnici omotaca	Bez stražara
Prečnik	250 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavcine	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	800 kg
Nosivost na 6 km/h	640 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2.15 kg




NOVATECH

ITP 250x50-Ø25-H160-soft cv

EAN 4031582329629

Broj porudžbine 00833104



BETTER MOBILITY. BETTER LIFE.