PRODUCT INFORMATION

# GALEA

5071YGP100P30-10

EAN 4031582354201



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●●○ |

## CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Galea |
| Type | Swivel castor with directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric Conductive | Yes |
| Stainless | No |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 139 mm |

## HOUSING

| | |
|---|---|
| Housing Material | Polyamide |
| Fork shape | Closed |
| Swivel Bearing | Two ball races |
| Offset | 40 mm |
| Swivel interference | 205 mm |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene, electric conductive |
| Tread Material Mix | Thermoplastic rubber, electric-conductive |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 30 mm |
| Hardness of tread (A) | 87 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Bolt hole |
| Bolt hole diameter | 10 mm |

© Copyright 2026 TENTE International GmbH


# GALEA


5071YGP100P30-10

EAN 4031582354201

BETTER MOBILITY. BETTER LIFE.

## Product Drawings



© Copyright 2026 TENTE International GmbH