



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ● ●
Movement noise	● ● ● ● ● ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea
Type	Swivel caster with combined lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	286.6 lb
Electric conductive	no
Stainless	no
Load capacity Static	573.2 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.89 in
Overall width	3.5 in
Overall weight	3.2 lb
Certification	Tested and monitored by TÜV Süd

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	2.05 in
Swivel radius	6.14 in
Swivel interference	12.28 in
Dome diameter	2.2 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	5.91 in
Tread width	0.87 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	3.54 in
Plate width	2.95 in
Plate hole length (Maximum)	2.95 in
Plate hole width (Maximum)	1.97 in
Plate hole diameter	0.43 in

LINEA


594CUAP150P51

EAN 4031582409031



BETTER MOBILITY. BETTER LIFE.

Product Drawings



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award