

# ALPHA STAINLESS

8470POO080P30-13 TFR

EAN 4031582480474



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	108 mm
Overall weight	0.66 kg

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	80 mm
Tread width	30 mm
Hardness of tread (D)	65 Shore D

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	44 mm
Swivel radius	80 mm
Swivel interference	160 mm
Stainless	✓

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

# ALPHA STAINLESS

8470POO080P30-13 TFR

EAN 4031582480474



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

8470...80P30-13

