PRODUCT INFORMATION

OMIKRON TWIN

9958FTP250P65

EAN 4031582316988




Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Omikron twin
Type	Fixed caster
Standard	similar EN12532 - Transport Equipment
Load capacity at 2.5 mph	6613.86 lb
Load capacity at 3.7 mph	5291.09 lb
Electric conductive	no
Stainless	no
Load capacity Static	9920.79 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	12.8 in
Overall width	6.06 in
Overall weight	46.54 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Housing Color	Transparent coating
Lubrication nipple	1
Dome diameter	6.3 in

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	9.84 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	7.87 in
Plate width	6.3 in
Plate hole length (Maximum)	4.72 in
Plate hole width (Minimum)	6.3 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.59 in

© Copyright 2026 TENTE International GmbH


OMIKRON TWIN


9958FTP250P65


EAN 4031582316988

Order number 00801478

Product Drawings







© Copyright 2026 TENTE International GmbH