

# PURETECH

PVR125X37-Ø12 HL48

EAN 4031582321272

Broj porudžbine 00030957



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●○○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,471 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	37 mm
dimenzija rupa osovina	12 mm
dužina glavčine	48 mm
Teškoća gazećeg omotac (A)	85 Šora A

# PURETECH

PVR125X37-Ø12 HL48

EAN 4031582321272  
Broj porudžbine 00030957



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

