

PRODUCT INFORMATION

# ELASTECH

UFC160X46@12X60

EAN 4031582422313



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL

Tread hardness	soft
Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.81 in
Axle hole diameter	0.47 in
Hub length	2.36 in
Hardness of tread (A)	64 Shore A

### PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	2.1 lb

# ELASTECH

UFC160X46@12X60

EAN 4031582422313



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

