

PRODUCT INFORMATION

PURETECH AIR

PQR260x85-Ø25 HL74 2PR

EAN 4031582321081



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Pneumatic tyre, block profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	260 mm
Tread width	85 mm
Axle Hole Diameter	25 mm
Hub Length	74 mm
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Puretech air
Type	Wheel
Load capacity at 3 km/h	150 kg
Electric Conductive	No
Stainless	No
Load capacity Static	150 kg
Overall weight	1.04 kg

PURETECH AIR

PQR260x85-Ø25 HL74 2PR

EAN 4031582321081

Order number 00031045
Product Drawings



BETTER MOBILITY. BETTER LIFE.

