

ALPHA STAINLESS

8478UFD160P63

EAN 4031582347173
Order number 00035539



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Stainless	✓
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall width	4.53 in
Overall weight	3.89 lb

WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Wheel color	Silver gray (RAL7001)
Diameter	6.3 in
Tread width	1.81 in
Body width	1.81 in
Hardness of tread (A)	63 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Color	Stainless steel

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

ALPHA STAINLESS

8478UFD160P63

EAN 4031582347173
Order number 00035539



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

