

PURETECH

PIR 160x40-Ø20

EAN 4031582320374



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	297.62 lb
Electric conductive	no
Stainless	no
Load capacity Static	595.25 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.87 lb

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.57 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Body width	1.57 in
Hardness of tread (A)	80 Shore A

PURETECH

PIR 160x40-Ø20

EAN 4031582320374

Order number 00023493

Product Drawings



BETTER MOBILITY. BETTER LIFE.

