PRODUCT INFORMATION

E-DRIVE ULTIMATE

EDUAUFF125P60

EAN 4031582478327

BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	E-Drive ultimate
Type	Drive Unit
Electric conductive	no
Stainless	no
Temperature range (Minimum)	41 °F
Temperature range (Maximum)	104 °F
Overall width	7.48 in
Overall weight	18.15 lb
Length	Max. 315 mm (emergency release actuated)
Wheel diameter	125 mm, wear limit Ã˜ 115 mm
Wheel tread	Solid rubber, non-marking, Shore A 63
Wheel width	1.38 in
Width	7.01 in
Maximum thrust force	32
Maximum lifting force / contact pressure force	400
Height in home position	5.51 in
Installation height	6.69 in
Emergency release	Mechanical
Protection type	IPX4 (splash water from all sides, all plugs plugged in)
Permissible ambient temperature	Operating temperature 5 Â°C to 40 Â°C, air humidity 90 %, non-condensing
Weight	17.64 lb
Maximum speed	2.49 mph
Ground clearance	1.18 in
Ground unevenness (Minimum)	-0.59 in
Ground unevenness (Maximum)	0.59 in
Permissible storage temperature (Minimum)	14 °F
Permissible storage temperature (Maximum)	113 °F

© Copyright 2026 TENTE International GmbH

E-DRIVE ULTIMATE

EDUAUFF125P60

EAN 4031582478327

Order number 00066143

HOUSING

Housing Material	Electric
Fork shape	Drive
Housing Color	Blue passivated

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Flanged wheel
Wheel color	Silver gray (RAL7001)
Diameter	4.92 in
Tread width	1.57 in
Body width	1.57 in
Hardness of tread (A)	63 Shore A

FITTING

Fitting type	Rectangular plate

© Copyright 2026 TENTE International GmbH


E-DRIVE ULTIMATE

EDUAUFF125P60

EAN 4031582478327

Order number 00066143

Product Drawings



© Copyright 2026 TENTE International GmbH