PRODUCT INFORMATION

DURATECH

TOP 082x54-Ø20 HL60

EAN 4031582322583



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.23 in
Tread width	2.13 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	2.13 in
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1058.22 lb
Electric conductive	no
Stainless	no
Load capacity Static	2645.54 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.87 lb

© Copyright 2026 TENTE International GmbH

DURATECH

TOP 082x54-Ø20 HL60

EAN 4031582322583

Order number 00804208

Product Drawings





