

# ALPHA STAINLESS

8470UFC125P62

EAN 4031582422399  
Order number 00303333



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	155 mm
Overall width	75 mm
Overall weight	1.071 kg

## WHEEL

Body material	Polyamide
Tread hardness	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (A)	63 Shore A

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	40 mm
Swivel radius	102.5 mm
Swivel interference	205 mm
Dome diameter	75 mm

## FITTING

Fitting type	Small rectangular plate
Plate length	105 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	9 mm

# ALPHA STAINLESS

8470UFC125P62

EAN 4031582422399  
Order number 00303333



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

8470U00125P62-neu

