

COMPACTA

2198UOI030P60-45x20

EAN 4031582030068



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Compacta
Type	Fixed caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	66.14 lb
Electric conductive	no
Stainless	no
Load capacity Static	132.28 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall height	1.34 in
Overall width	0.79 in
Overall weight	0.07 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Angular
Housing Color	Blue passivated
Dome diameter	0.79 in

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	1.18 in
Tread width	0.59 in
Body width	0.59 in
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	1.77 in
Plate width	0.79 in
Plate hole length (Maximum)	1.38 in
Plate hole width (Maximum)	1.38 in
Plate hole diameter	0.22 in

COMPACTA

2198UOI030P60-45x20

EAN 4031582030068

Order number 00021134

Product Drawings



BETTER MOBILITY. BETTER LIFE.

