

DURATECH

UOP200X50-Ø20 HL60

EAN 4031582442847



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Axle hole diameter | 20 mm |
| Hub length | 60 mm |
| Hardness of tread (D) | 75 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Duratech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 900 kg |
| Load capacity Static | 1800 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 1.006 kg |

DURATECH

UOP200X50-Ø20 HL60

EAN 4031582442847



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

