

ALPHA STAINLESS

8478PJD160P63 TFR

EAN 4031582386806



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	7.87 in
Overall weight	3.19 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Diameter	6.3 in
Tread width	1.81 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Stainless	✓

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.53 in
Plate hole length (Maximum)	4.13 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.43 in