

PRODUCT INFORMATION

NOVATECH

FTP 160X50-Ø25 HL60

EAN 4031582329568
Order number 00837289



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2425.08 lb
Load capacity at 3.7 mph	1984.16 lb
Load capacity Static	3306.93 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	6.3 lb

NOVATECH

FTP 160X50-Ø25 HL60

EAN 4031582329568
Order number 00837289



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

