

# AGILA

2470DYK100P30-11

EAN 4031582341607



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila                     |
| CO2 emission (scope 3)      | 1.75                      |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 80 kg                     |
| Electric Conductive         | Yes                       |
| Stainless                   | No                        |
| Load capacity Static        | 160 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 85 °C                     |
| Overall Height              | 135 mm                    |
| Overall width               | 60 mm                     |
| Overall weight              | 0.84 kg                   |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel Bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 38 mm               |
| Swivel radius       | 88 mm               |
| Swivel interference | 176 mm              |
| Dome diameter       | 60 mm               |

## WHEEL

|                       |                                          |
|-----------------------|------------------------------------------|
| Body material         | Sheet Steel                              |
| Tread Material Mix    | Solid rubber, black, electric-conductive |
| Bearing               | Cone ball bearing                        |
| Wheel Color           | Blue passivated                          |
| Threadguards          | With threadguard                         |
| Diameter              | 100 mm                                   |
| Tread width           | 32 mm                                    |
| Body width            | 32 mm                                    |
| Hardness of tread (A) | 80 Shore A                               |

## FITTING

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Fitting type       | Bolt hole                                                  |
| Bolt hole diameter | 11 mm                                                      |
| Hint               | Castors can be mounted with standard screws of any length. |

# AGILA

2470DYK100P30-11

EAN 4031582341607

Order number 00006519

Product Drawings



BETTER MOBILITY. BETTER LIFE.

