

S70-10X15 / 10 DRILLED STEM

EAN 4031582411904



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Overall height	0.24 in
Overall weight	0.06 lb

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.59 in