

# STEM

S70-10X15 / 10 DRILLED STEM

EAN 4031582411904



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Corrosion resistance ● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Stem
Type	Accessory
Load capacity at 1.8 mph	176.37 lb
Load capacity Static	352.74 lb
Overall height	0.24 in
Overall weight	0.06 lb

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.39 in
Stem length	0.59 in