

# MAXTECH

PNP200X45-Ø8 MS

EAN 4031582320640



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	polipropilen
	mekan
materijal omotaca	Poliuretanski, penasti
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	45 mm
dimenzija rupa osovina	8 mm
dužina glavcine	53 mm
Teškoća gazećeg omotac (A)	70 Šešelj A

## PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Tip	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	70 kg
Statički Nosivost	140 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,555 kg

# MAXTECH

PNP200X45-Ø8 MS

EAN 4031582320640



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

