PRODUCT INFORMATION

NOVATECH

RK.ETP075X80-Ø47X14

EAN 4031582369519

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	75 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A
Ball bearing diameter	47 mm
Ball bearing width	14 mm

PERFORMANCE

Roll performance	●●●●○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 3 km/h	700 kg
Load capacity Static	1400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

© Copyright 2025 TENTE International GmbH

NOVATECH

RK.ETP075X80-Ø47X14

EAN 4031582369519

BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS







© Copyright 2025 TENTE International GmbH