

# NOVATECH

ETP 120X50-Ø25 HL50

EAN 4031582369489

Broj porudžbine 00827826



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	480 kg
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,04 kg

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	120 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavcine	50 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6304

# NOVATECH

ETP 120X50-Ø25 HL50

EAN 4031582369489

Broj porudžbine 00827826



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

