PRODUCT INFORMATION

KAPPA LOAD

9658FTP250P64 TFR

EAN 4031582386332

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Kappa load
Type	Fixed caster
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	4232.87 lb
Load capacity at 3.7 mph	3527.39 lb
Electric conductive	no
Stainless	no
Load capacity Static	8465.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	12.01 in
Overall weight	38.5 lb

HOUSING

Housing Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Lubrication nipple	1

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	9.84 in
Tread width	3.15 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	6.89 in
Plate width	5.51 in
Plate hole length (Maximum)	5.51 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.59 in

© Copyright 2026 TENTE International GmbH


KAPPA LOAD

9658FTP250P64 TFR

EAN 4031582386332

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH