

# AGILA

2478PJP125P30

EAN 4031582472158



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad

## FITTING

Fitting type	Bolt hole
Hint	Castors can be mounted with standard screws of any length.

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Housing type	Fixed castor

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm

# AGILA

2478PJP125P30

EAN 4031582472158



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

