

# FOOTMASTER

FOOT MASTER GD-120-F-NYN-CAL

EAN 4031582413267



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ○ ○ ○ ○ ○ |
| Movement noise       | ○ ○ ○ ○ ○ |
| Attrition            | ○ ○ ○ ○ ○ |
| Corrosion resistance | ○ ○ ○ ○ ○ |

## CORE ATTRIBUTES

|                             |               |
|-----------------------------|---------------|
| Product name                | Footmaster    |
| Type                        | Swivel caster |
| Load capacity at 1.8 mph    | 2204.62 lb    |
| Electric conductive         | no            |
| Stainless                   | no            |
| Load capacity Static        | 2204.62 lb    |
| Temperature range (Minimum) | 14 °F         |
| Temperature range (Maximum) | 194 °F        |
| Overall height              | 4.72 in       |
| Overall width               | 3.94 in       |
| Overall weight              | 3.97 lb       |

## HOUSING

|                     |         |
|---------------------|---------|
| Housing Color       | White   |
| Offset              | 2.05 in |
| Swivel radius       | 3.5 in  |
| Swivel interference | 7.01 in |
| Dome diameter       | 3.94 in |

## WHEEL

|             |                        |
|-------------|------------------------|
| Bearing     | Roller bearing, damped |
| Wheel color | Black                  |
| Diameter    | 2.95 in                |
| Tread width | 1.2 in                 |
| Body width  | 1.2 in                 |

## FITTING

|                             |         |
|-----------------------------|---------|
| Plate length                | 3.74 in |
| Plate width                 | 3.74 in |
| Plate hole length (Maximum) | 2.76 in |
| Plate hole width (Maximum)  | 2.76 in |
| Plate hole diameter         | 0.43 in |

# FOOTMASTER

FOOT MASTER GD-120-F-NYN-CAL

EAN 4031582413267

Order number 00062072  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

