

DURATECH

TOP 082X54-Ø20 HL60

EAN 4031582322583
Order number 00804208



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	82 mm
Tread width	54 mm
Axle hole diameter	20 mm
Hub length	60 mm
Body width	54 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.396 kg

DURATECH

TOP 082X54-Ø20 HL60

EAN 4031582322583
Order number 00804208



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

