

NOVATECH

ITP 100x50-Ø25

EAN 4031582319866



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK


Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavnice	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ● ○
Buka u pokretu	● ● ● ● ○ ○
Ishrana	● ● ● ● ● ○
otpornost na rdju	● ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	540 kg
Nosivost na 6 km/h	430 kg
Električni provod	no
nerdjajući	no
Statički Nosivost	1080 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0.59 kg




NOVATECH

ITP 100x50-025

EAN 4031582319864

Broj porudžbine 00830808



BETTER MOBILITY. BETTER LIFE.