PRODUCT INFORMATION

# ALPHA

## 3499UFP160P67 Q2-13

EAN 4031582381139



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●●● |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Alpha |
| Type | Customized solution |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 661.39 lb |
| Load capacity at 3.7 mph | 440.92 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 1322.77 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 7.87 in |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, heavy |
| Fork shape | Broad |
| Housing Color | Blue passivated |

### WHEEL

| | |
|---|---|
| Tread hardness | soft |
| Body material | Polyamide |
| Tread material | Elastic tire, non-marking, vulcanized |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Threadguards | With threadguard |
| Diameter | 6.3 in |
| Tread width | 1.81 in |
| Hardness of tread (A) | 64 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Plate with central locking |
| Plate length | 5.39 in |
| Plate width | 4.53 in |
| Plate hole length (Maximum) | 4.13 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 3.15 in |
| Plate hole diameter | 0.43 in |

© Copyright 2026 TENTE International GmbH


# ALPHA


3499UFP160P67 Q2-13


EAN 4031582381139


TENTE
BETTER MOBILITY. BETTER LIFE.

## Product Drawings






© Copyright 2026 TENTE International GmbH