

NOVATECH

ITP125X40-Ø15-HL40-80SHA

EAN 4031582481488



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Aluminium |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 40 mm |
| Axle hole diameter | 15 mm |
| Hub length | 40 mm |
| Hardness of tread (A) | 80 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Novatech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 250 kg |
| Load capacity Static | 500 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 0.804 kg |

TECHNICAL DRAWINGS

