

MAXTECH

UAP100X40-Ø15 HL44 BURDEOS

EAN 4031582442564



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	40 mm
Axle hole diameter	15 mm
Hub length	44 mm
Hardness of tread (D)	40 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.233 kg

MAXTECH

UAP100X40-Ø15 HL44 BURDEOS

EAN 4031582442564



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

