

# ALPHA

3477POO100P30-13

EAN 4031582305500



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●●

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	125 kg
Statički Nosivost	250 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	128 mm
Ukupna težina	0,894 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	36 mm
Teškoća gazećeg omotac (D)	65 Šor D

## KUCISTE

Materijal	Čelični list, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	41 mm
okretni radijus	121 mm
Otpor okretanju	242 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

# ALPHA

3477POO100P30-13

EAN 4031582305500



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

