

ELASTECH

EEZ250x60-Ø190 DG

EAN 4031582318340



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Tread hardness	mekan
Materijal za telo	Čelik, gvožđe
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	Borehole, neobrađen
Prečnik	250 mm
Širina omotac	60 mm
dimenzija rupa osovina	190 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	630 kg
Nosivost na 6 km/h	525 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1260 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	1.36 kg

ELASTECH


EEZ250x60-Ø190 DG

EAN 4031582318340

Broj porudžbine 00830877
Crteži proizvoda



BETTER MOBILITY. BETTER LIFE.




ELASTECH

EEZ250x60-Ø190 DG

EAN 4034582318340

Broj porudžbine 00830877



BETTER MOBILITY. BETTER LIFE.