

# LUMINA

AA25PJ1050B10 11x20 TFR

EAN 4031582399943



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product Name                | Lumina                         |
| Type                        | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 3 km/h     | 40 kg                          |
| Electric Conductive         | No                             |
| Stainless                   | No                             |
| Load capacity Static        | 80 kg                          |
| Temperature range (Minimum) | -10 °C                         |
| Temperature range (Maximum) | 40 °C                          |
| Overall Height              | 58 mm                          |
| Overall width               | 55 mm                          |
| Overall weight              | 0.09 kg                        |

## HOUSING

|                     |                            |
|---------------------|----------------------------|
| Housing Material    | Polypropylene              |
| Fork shape          | Twin wheel housing, closed |
| Swivel Bearing      | Stem, swiveling            |
| Swivel radius       | 63 mm                      |
| Swivel interference | 126 mm                     |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread Material Mix    | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Threadguards          | Without threadguard            |
| Diameter              | 50 mm                          |
| Tread width           | 10 mm                          |
| Hardness of tread (A) | 87 Shore A                     |

## FITTING

|               |                                  |
|---------------|----------------------------------|
| Fitting type  | Stem with grip ring, with collar |
| Stem diameter | 11 mm                            |

# LUMINA

AA25PJ1050B10 11x20 TFR

EAN 4031582399943



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

