

NOVATECH

ETY 080X20-Ø25 HL12

EAN 4031582365382
Order number 00835789



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	80 mm
Tread width	20 mm
Axle hole diameter	25 mm
Hub length	12 mm
Body width	20 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	140 kg
Load capacity at 6 km/h	110 kg
Load capacity Static	280 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.3 kg

NOVATECH

ETY 080X20-Ø25 HL12

EAN 4031582365382
Order number 00835789



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

