

NOVATECH

ITP 125X30-Ø15 HL45

EAN 4031582319873

Broj porudžbine 00829478



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
štitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	30 mm
dimenzija rupa osovina	15 mm
dužina glavčine	45 mm
Širina tela	30 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

PERFORMANSE

Performanse kotrljanja ●●●●○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	420 kg
Nosivost na 6 km/h	335 kg
Statički Nosivost	840 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,48 kg

NOVATECH

ITP 125X30-Ø15 HL45

EAN 4031582319873

Broj porudžbine 00829478



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

