

# AGILA

2471PJP125R05-25.4

EAN 4031582427011



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                     |
|-----------------------------|-------------------------------------|
| Product name                | Agila                               |
| Housing type                | Swivel castor with directional lock |
| Standard                    | EN12530 - Devices Castors           |
| Load capacity at 3 km/h     | 100 kg                              |
| Load capacity Static        | 200 kg                              |
| Temperature range (Minimum) | -20 °C                              |
| Temperature range (Maximum) | 60 °C                               |
| Overall height              | 163 mm                              |
| Overall weight              | 1.143 kg                            |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 32 mm                  |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 41 mm               |
| Swivel radius       | 131 mm              |
| Swivel interference | 262 mm              |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 25.4 mm           |
| Bolt length   | 45 mm             |

# AGILA

2471PJP125R05-25.4

EAN 4031582427011



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

